

Passive re-defined


Sordin Seal is Sordin's firm response to industries seeking safe, modern and cost-effective hearing protection for their employees. And, of course, others who share the same aspirations.

Sordin Seal re-defines the concept of passive hearing protection with its many elaborately engineered features. There are many passive hearing protectors out there which meet the necessary attenuation criteria – thus ensuring the user's health and safety. Sordin Seal is just a little bit more technologically advanced.

We carefully reviewed important user criteria when designing Sordin Seal. The primary one being – keeping your hearing protector on for as long as you're exposed to harmful noise! Here, already, many products fail and are taken on and off by users, or even left in the lockers in the first place.

While Sordin Seal dampens noise more effectively than most comparable hearing protectors, that's only part of the reason your employees will like them and keep them on all day. It is also lightweight, it fits perfectly around the ears without pressing uncomfortably hard, and it stays firmly in place thanks to e.g. an additional, flexible support head band.

It's also easy to buy and get started in large scale with Sordin Seal. The hearing protector comes with only one attenuation level, comparable to industry-standard Medium, which makes it suitable for most professional or industrial noise environments.



Passive hearing protection – an active safety measure

While both sound and hearing are complex sciences, their essence can be very easily summarized: Use hearing protection!

It takes surprisingly little noise to cause hearing loss. What many don't know, or think about, is that all hearing loss is permanent. So, be careful and wear a hearing protector even if you're at the lower end of, or even slightly below, the risk exposure level! Especially when it's so easy and straight-forward to avoid life-long hearing loss.

First, choose between a passive or electronic hearing protector. Sordin Seal is passive, which means that it uses mechanical noise suppression only. In contrast, electronic hearing protectors combine mechanical suppression with some type of digital audio processing technology, along with for example radio and streaming functionality.

Passive hearing protection is fully adequate for many purposes.
Unless you want to be able to listen to music, hear ambient sound or communicate electronically, you are generally well off with a high-quality, cost-efficient passive hearing protector like Sordin Seal.

Some useful facts

Passive vs. electronic


Sordin Seal is a passive hearing protector, which means that it uses mechanical noise suppression technology only. With electronic hearing protectors, this is complemented by microphones on the outside of the muffs, which pick up sound, amplify it and deliver it to the user's ears electronically. These products may also include additional features such as FM radio and communications capabilities.

dB vs. dB(A)

Decibel (dB) is the general measure of sound level, or loudness. There are, however, numerous variants and in this brochure, we address dB and dB(A). In simplified terms, dB is the intrinsic loudness of a sound source, while dB(A) is the loudness subjected to a person's hearing when exposed to noise. Hence dB(A) depends on factors such as the distance to the source and whether you're wearing a hearing protector or not.

Harmless vs. harmful noise

There is no clear dB(A) limit where noise becomes harmful. Directives are based on a combination of noise level and exposure time According to the Swedish Work Environment Authority, a hearing protector should have a daily noise exposure index (LEX), of "8 h, 80 dB(A)". This is equivalent to 8 hours of continuous exposure at 80 dB(A), or 4 hours at 83 dB(A). At LEX "8 h, 85 dB(A)", hearing protection is mandatory – requirements met by Sordin Seal in most noise environments.



frequency as "high or low pitch", both of which are tested in regular hearing tests. A common indicator of harmless sound is below 85 dB(A), although also partly dependent on frequency. See page 5 for more information on harmless vs. harmful sound.

The range of human hearing depends on sound level and frequency. We all know sound level as "loud or weak", and

160
140
120
Harmful zone
100
88
85 dB(A)
Hearing
40
Speech
20
100 20 50 100 200 500 1000 2000 5000 10000 20000

An unbeatable trio

With its medium-level attenuation, Sordin Seal is the perfect all-round product for most professional purposes.

Sometimes, there's a need for additional functionality. Then Sordin Seal's electronic "siblings" come in to beautifully complement your hearing protector range.

We let Sordin Seal stand as the design model when developing our two most advanced hearing protectors to date, designed specifically for professional use: Sordin Sharp and Sordin Share.

Our decision to base these two high-end products – both featuring novel designs and launched in 2021 – on Sordin Seal says a lot about our trust in the product. Sordin Sharp and Sordin Share lend several features to Sordin Seal, including material selection, cup shape and the unique headband design.

Weight may be an issue with electronic hearing protectors and Sordin Sharp and Sordin Share owe their relatively low weight to the slim Sordin Seal design. Similarly, its excellent robustness makes all three products equally suitable for use in harsh industrial environments.

Combined, Sordin Seal, Sordin
Sharp and Sordin Share offer a
future-proof investment path for
professional hearing protection.
This unbeatable trio will cover
every need you may experience
in future – whether for pure health
and safety purposes using Sordin
Seal, or for the added value of e.g.
Bluetooth Multipoint connectivity,
ambient sound and advanced
communications capabilities provided by
Sordin Sharp and Sordin Share.

S@RDIN

For detailed information, see Sordin Sharp and Sordin Share brochures.

Sordin Seal

Sordin Seal is your ideal all-round hearing protector suitable for medium-level noise. It provides safe protection, while offering the comfort necessary for all-day use – sitting firmly in place for optimum noise attenuation, without pressing too hard on your head.



Sordin Share re-defines the very concept of hearing protection. It comes with unique team-intercom capabilities and allows for app-controlled setup and management of user groups.

Each Sordin Share unit forms part of a mesh network, enabling medium-range direct communication between group members.

Sordin Sharp

Sordin Sharp comes with built-in Bluetooth® Multipoint support. You can therefore, for example, connect up to two cell phones or one cell phone and a com radio – providing functionality ranging from music or audio book entertainment to advanced communications with colleagues.

Sordin Seal features

UU **Headband or helmet version** Sordin Seal is available in headband and helmet versions. The helmet version is compatible with many popular helmet brands and models in the market by using an adapter. Large cup volume Despite its slim design, Sordin Seal offers plenty of ear space inside the cups - making it comfortable to wear Wide sealing rings Modern design A slim and slick shape makes people Just like its cups, Sordin Seal's sealing rings offer plenty of ear space, want to wear Sordin Seal. Thanks to its

ensuring a perfect individual fit even

for large user groups.

The image below is a collage of different Sordin Seal models and configurations. For a detailed product specification, see page 10-11.



modern look, we even used Sordin Seal

as the design model for our high-end

electronic products Sordin Sharp and

Specifications

TECHNICAL INFORMATION

ABS
PU
ABS, PP, TPE, PU foam
РОМ
PA
TPE
PA
PA
PP
Stainless steel
-20°C to +55°C
236 grams / 233 grams
REACH

APPROVED HELMET COMBINATIONS

Helmet	Adapter	Sizes
Petzl Vertex	21	S, M, L

For latest supported helmet combinations, please visit www.sordin.com/seal

PRODUCT NUMBERS

Product No	Description	Cup Colour
814004	Sordin Seal Headband Black	Black
814007-10T	Sordin Seal Headband Yellow Hi-Viz	Yellow Hi-Viz
814004-3021T	Sordin Seal Helmet Mounted Adapter 21 Black	Black
81H-4001T	Sordin Seal Hygiene Kit (for all Sordin Seal versions)	

EN APPROVALS

COMPLIANCE AND APPROVALS

The products meet the Essential Health and Safety Requirements as laid out in Annex II and conforms with quality assurance of the production process, module D, laid out in Annex VIII of the PPE-regulation (EU) 2016/425. CE markings are in accordance with EN 352-1:2020 and EN 352-3:2020. The products are approved to modules B and D by BSI (NB 2797), BSI Group The Netherlands B.V. Say Building, John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands.



ATTENUATION DATA



				Н	M	L	SNR	NRR
Sordin Seal headband			33 dB	28 dB	22 dB	31 dB	25 dB	
Frequency (Hz)	63	125	250	500	1 000	2 000	4 000	8 000
Mean attenuation, M _f (dB)	18.6	19.7	20.8	27.8	32.6	32.7	39.8	40.0
Standard Deviation, s _f (dB)	3.0	2.1	1.8	2.4	2.3	2.0	2.7	2.5
APV (M _f - s _f) (dB)	15.6	17.5	19.0	25.4	30.3	30.7	37.1	37.5



				Н	M	L	SNR	NRR
Sordin Seal helmet			33 dB	27 dB	22 dB	30 dB	24 dB	
Frequency (Hz)	63	125	250	500	1 000	2 000	4 000	8 000
Mean attenuation, M _f (dB)	18.2	18.9	20.3	26.3	31.2	33.1	40.3	40.3
Standard Deviation, s _f (dB)	3.1	2.4	2.1	2.5	1.8	3.0	3.5	3.6
APV (M _f - s _f) (dB)	15.1	16.5	18.2	23.8	29.4	30.1	36.9	36.6

10 11

